

An innovative solution

- A compact design, it integrates a larger number of sockets adapted to IT environments, facilitating connection.
- A modern design that can be installed on the floor or on a desk, or also be mounted to the wall.

Protection adapted to meet all your needs

- 5 or 6 output sockets (5 british standard, 6 italian / schuko or french standard) for easy distribution directly to your applications:
 - 4 sockets protected against power cuts and over voltages, aimed at your most sensitive applications (central systems, monitors). The back-up time, able to last up to 30 minutes, enables a standard PC configuration to be saved.
 - 2 sockets (1 for BS) protected against over voltages alone for use with less critical applications (1200 VA) and high absorption consumers (laser printers).

Protection for your phone line

- Protection for the telephone / modem / ADSL line (RJ11 connector) against the risk of on-line overvoltage.

Easy to use

- Operating mode indicated by means of the mimic panel connected to the status indicator lights and the **UNI VISION** communication software.
- Easy battery maintenance (user replaceable).

HIGH
FREQUENCY UPS

2 YEAR GUARANTEE




Your protection for

- > PC: LCD or CRT monitors, scanners, printers, etc.
- > Cash registers
- > Interactive terminals




Connections



1. Filtered output sockets
2. Inverter output sockets
3. Input socket and fuse
4. Telephone / modem line protections
5. RS232 / USB serial port
6. Battery replacement flap
7. Bracket for wall mounting

Control panel



Communication option

- **UNI VISION** software for the control and automatic shutdown of applications connected to Windows™ and Linux. Free to download from our website: www.socomec.com.

Technical data

MODELS	NETYS PL 550	NETYS PL 750
ITEM CODE	NET550F-PL	NET750F-PL
UPS power	550 VA (330 W)	750 VA (450 W)
Power (surge)	1200 VA	1200 VA
Input	230 V (170 ÷ 260 V) ; 50 / 60 Hz with automatic selection	
Output	230 V nominal ; 50 / 60 Hz	
Output socket	6 sockets: n° 4 UPS and n° 2 surge (over voltage)	
Telephone protection	telephone line / modem / ADSL input / output: RJ11	
BATTERIES		
Type	sealed lead-acid maintenance free - expected life 3 / 5 years	
Back-up time ⁽¹⁾	20 min.	30 min.
COMMUNICATION		
Interface	RS232 and USB serial port (free software via Internet)	
ENVIRONMENT		
Dimensions W x D x H (mm)	160 x 210 x 125	
Weight	5.3 kg	5.5 kg
Reference standards	(EN) IEC 62040-1-1 (safety), EN 50091-2 / IEC 62040-2 (EMC), EN 61000-4-5 / C62.41: 1991 (over voltages)	

(1) PC + 15" LCD monitor.

Single-phase
UPS

NETYS PE

from 400 to 1000 VA

top of the range electrical protection

A PERSONAL configuration

- Adapted to protect office applications.
- A range of four nominal voltages.

A solution to network power cuts and voltage variations

- Thanks to the integrated AVR function (Automatic Voltage Regulation).

Adapted connection

- Computer usage on IEC 320 sockets (IT standard).

Protection for your phone line

- Protection for the phone line⁽²⁾/modem/ADSL (RJ11 connector) on the 600 to 1000 VA models.

Easy to use

- Control panel with LEDs allowing the operating mode to be easily monitored.

Communication with the computer system

- RS232 and USB advanced connections for management of the power supply and of the controlled automatic shutdown of applications via PC (NETYS PE 600 to 1000 VA models).

INTERACTIVE LINE
WITH AVR

2 YEAR GUARANTEE



NETYS PE
400/600/800 VA



NETYS 002 B 1 CAT

NETYS PE
1000 VA




NETYS 004 B 1 CAT

Your protection
for

- > CAD, graphic workstations
- > Multimedia workstations and peripherals
- > LCD or CRT monitors



Connections




1. RS232/USB serial port
2. Phone/modem line protection
3. UPS output sockets

4. Input socket and fuse
5. Fan/air vents

Communication option

- **UNI VISION** software for the control and automatic shutdown of applications connected to Windows™ and Linux. Free to download from our website: www.socomec.com.

Control panel



Technical data



MODELS	NETYS PE 400	NETYS PE 600	NETYS PE 800	NETYS PE 1000
ITEM CODE	NET0400-PE	NET0600-PE	NET0800-PE	NET1000-PE
UPS power	400 VA (240 W)	600 VA (360 W)	800 VA (480 W)	1000 VA (600 W)
Input	230 V (170 ÷ 280 V) ; 50 / 60 Hz with automatic selection			
Output	230 V nominal ; 50/60 Hz			
Output sockets	3 IEC 320			4 IEC 320
Telephone protection ⁽²⁾	-	telephone line/modem/ADSL input/output: RJ11		
BATTERIES				
Type	sealed lead - acid maintenance free - expected life 3 / 5 years			
Back-up time ⁽¹⁾	8 min.	15 min.	20 min.	45 min.
COMMUNICATION				
Interface	-	RS232 and USB serial port (free software via Internet)		
ENVIRONMENT				
Dimensions W x D x H (mm)	99 x 334 x 143			140 x 370 x 180
Weight	5.0 kg	6.1 kg	6.6 kg	13.6 kg
Reference standards	(EN) IEC 62040-1-1 (safety), EN 50091-2/IEC 62040-2 (EMC), EN 61000-4-5/C62.41: 1991 (over voltage)			

(1) PC + LCD monitor 15". (2) Option for some countries.

A PROFESSIONAL UPS

- Designed for professional environments, protection against power cuts and over voltage is ensured by Line Interactive technology with automatic voltage regulation (AVR).

An installation adapted to the environment

- It can even be installed as a Tower, Mini-Tower or 19" Rack, depending on the user's needs.

Simplified maintenance

- Battery 'hot swap', without closing down other applications.
- Battery can be changed from the front in rack installations.
- Battery check system and replacement indicator.

Adapted connections

- Easy connections to the applications (depending on power) via 6 or 8 IEC 320 (IT standard) sockets.

A secure UPS

- EPO (Emergency Power Off) emergency stop.

Data line protection

- With RJ45 connector.

Communication with the computer system

- RS232 or USB* advanced connections for the management of the power supply and local/remote shutdown of applications.
- Advanced diagnostics and remote control via various protocols and environments of use: JBUS, HID, SNMP, TCP/IP.

* USB models from 1500 to 3000 VA.

INTERACTIVE LINE WITH
AVR - SINUSOIDAL OUTPUT

2 YEAR GUARANTEE



NETYS PR
1000 VA



NETYS PR
1500/2000 VA



NETYS PR
3000 VA



NETYS PR
1500/2000 VA Rack

Your protection
for

- > Professional and IT equipment
- > Servers and Networking devices
- > CAD/graphic workstations with monitors and peripherals
- > Control systems



