

ATyS M

Modular Transfer Switching Equipment
from 40 to 160 A



When **energy** matters


 **socomec**
Innovative Power Solutions

Why do you need Transfer Switching Equipment (TSE)?

Power outages can occur, even in high reliability distribution networks, leading to major incidents and losses on critical applications :

- emergency systems,
- healthcare facilities,
- server rooms,
- production lines.

To maximize your power availability, the Socomec range will safely transfer from any unstable or lost source to an alternate source. Furthermore, we ensure that you are prepared at all times thanks to our unique safety functions that facilitate maintenance on your low voltage electrical installation.



All-in-one TSE is the best choice for your application

Contact us to find out how your application could benefit from ATyS M.



HVAC redundant power supply

Cooling systems in data centers and other critical applications are an essential part of the electrical installation. By ensuring that the HVAC units have redundancy in terms of power supply, the effectiveness and profitability of your business are guaranteed.

Compact electrical distribution boards

The footprint is often a main driver in the design of an electrical installation. With ATyS M, space will no longer be a problem. Its compact modular design minimises the enclosure size, allowing it to be installed even in reduced spaces.



High rise buildings

Transfer switches are usually installed in high rise buildings to provide redundancy by supplying each floor with two independent risers and emergency sources. This type of installation dramatically reduces the risk of fire and the number of power outages throughout the building.

Why choose Socomec's *ATyS M*?



Constant power availability keeps your activity safe and efficient. At Socomec, we have been designing, manufacturing and testing switchgear since 1922 and guarantee safe, reliable and long lasting Transfer Switching Equipment (TSE) for your electrical installation. All our solutions are fully compliant with Class PC of IEC 60947-6-1, the international product standard for TSE.

Today, more than 3 million installations and major integrators worldwide are secured with a Socomec transfer switch. Each day, their smile is ON knowing that their operations will always keep on running.



Quick & easy installation

- DIN rail or back plate mounting
- Easy commissioning
- Accessible wiring



Easy to order

All-in-one product (controller and switch), ready to use thereby reducing the risk of incorrect wiring or assembly.



Proven technology

Integrated solution that has been engineered and tested according to IEC 60947-6-1 Class PC standard requirements for transfer switching.



Safe operation


Operators can always execute a manual transfer even under load supply.




Space saving


Side-by-side configuration allowing the ATyS M to fit into any 18 module standard enclosure (low-depth). Can be mounted in all positions and orientations.

Main features





















Get connected with *ATyS p M*





A solution for every application

Manual	Remotely operated	Automatic	Enclosed
 SIRCO VM1	 ATyS S & d S  ATyS d M	 ATyS t M & g M  ATyS p M	 <div>< 160 A > 125 A</div>
 SIRCOVER  SIRCOVER Bypass	 ATyS r  ATyS d H	 ATyS g  ATyS p	
DC	Static	Bypass	
 SIRCOVER PV	 ATyS S DC  ATyS r DC	 STATYS	 ATyS Bypass

Socomec: our innovations supporting your energy performance

1 independent manufacturer

3,600 employees
worldwide

10 % of sales revenue
dedicated to R&D

400 experts
dedicated to service provision

Your power management expert



POWER
SWITCHING



POWER
MONITORING



POWER
CONVERSION



ENERGY
STORAGE



EXPERT
SERVICES

The specialist for critical applications

- Control, command of LV facilities
- Safety of persons and assets
- Measurement of electrical parameters
- Energy management
- Energy quality
- Energy availability
- Energy storage
- Prevention and repairs
- Measurement and analysis
- Optimisation
- Consultancy, commissioning and training

A worldwide presence

12 production sites

- France (x3)
- Italy (x2)
- Tunisia
- India
- China (x2)
- USA (x3)

28 subsidiaries and commercial locations

- Algeria • Australia • Belgium • China • Canada
- Dubai (United Arab Emirates) • France • Germany
- India • Indonesia • Italy • Ivory Coast • Netherlands
- Poland • Portugal • Romania • Serbia • Singapore
- Slovenia • South Africa • Spain • Switzerland
- Thailand • Tunisia • Turkey • UK • USA

80 countries

where our brand is distributed

India corporate office

Socomec Innovative Power Solutions Pvt. Ltd.

B1, II Floor
Thiru-Vi-Ka Industrial Estate
Guindy, Chennai - 600 032
Tel: +91 44 3921 5400 / 5466
Mob: +91 9711229993, +91 9940633654
info.in@socomec.com



Manufacturing facility

Socomec India Private Limited.

756 Pace City II
Sector 37
Gurgaon - 122 001
Haryana
Tel: +91 124 4562700, 4597803
Fax: +91 124 4562733
CIN: U00000HR1999PTC038504

Regional & resident offices

Ahmedabad : +91 8939008184, +91 9727753931
Bengaluru : +91 9886323448, +91 9972578171
Chandigarh : +91 9023154784
Chennai : +91 9940147003
Cochin : +91 8939550688, +91 9745012322
Coimbatore : +91 8939550688, +91 9003032012
Hyderabad : +91 9642528800, +91 9959444277
Indore : +91 9827674469
Kolkata : +91 7550078077, +91 8697709095
Mumbai : +91 9987052602, +91 8879791802
New Delhi : +91 9953595413, +91 9958591713
Pune : +91 8793144968, +91 9987052604
Trivandrum : +91 9020179364
Vadodara : +91 9099947988
Vijaywada : +91 9515100473

HEAD OFFICE

SOCOMEK GROUP

SAS SOCOMEK capital 10 589 500 €
R.C.S. Strasbourg B 548 600 149
B.P. 60010 - 1, rue de Westhouse
F-67235 Benfeld Cedex
Tel. +33 3 88 57 41 41 - Fax +33 3 88 57 78 78
info.sop.isd@socomec.com

YOUR DISTRIBUTOR / PARTNER

www.socomec.co.in

